Materials 316L Stainless Steel


Pressure 35 Bar Ports 1/4" or 1/2" Membrane 2x MT.101.□

STM304 membrane housings uses two porous PTFE membranes, which are supported by sintered porous stainless steel discs on the outlet side. Any liquid in the gas sample will flow to the drain port. This port can also be used as a bypass function for the main flow.

The housing design allows the membranes to be changed without disconnection the port fittings.

Standard housings have NPT ports and include Viton seals. Other seal types are available as an option. BSPT and BSPP port types are also available.

The housings are free from welds and comply with NACE MR-01-75.





## **Technical Specifications**

Housing Model	STM304.221	STM304.441
Port Size	1/4" NPT	1/2" NPT
Drain & Bypass Ports	1/4" NPT	1/2" NPT
Maximum Pressure, Bar	35	35
Maximum Temperature, °C (1)	150	150
Materials of Construction (2)		
Head, Bowl & Internals	316L SS	316L SS
Seals (3)	Viton	Viton
Membrane Code (4)	2x MT.101.□	2x MT.101.□
Principal Dimensions in mm		
Diameter	150	150
Height	74	89
Volume, cc	50	50
Weight, kg	7.50	7.50
Accessories		
Mounting Bracket	MB.SM304	MB.SM304

## Notes

- (1) Maximum temperature of 150°C is due to the PTFE membrane
- (2) Material abbreviations, 316L SS = 316L Stainless Steel
- (3) Add suffix for other seal types, PTFE = .T, Chemraz = .C, Nitrile = N, Kalrez = .K, EPDM = .E, Silicone = .S, (e.g. STM304.221.T)
- (4) Replace the  $\Box$  with the membrane grade required, e.g. MT.101.M2



## **Contact Us**

Classic Filters Ltd.
Sextant Park
Neptune Close
Rochester
Kent
England
ME2 4LU

T +44 (0)1634 724224

F +44 (0)1634 724234

E info@classicfilters.com

W www.classicfilters.com

## **Follow Us**



http://www.linkedin.com/company/classic-filters-ltd.



http://www.twitter.com/classicfilters